

Daylight Deluxe Fluorescent Lamps

Cooler color appearance fluorescent lamps



Courtesy — Michael Mathers

Ideal for...

- Fluorescent general lighting in Industrial, Education, Healthcare and Residential applications



- **6500K Color Temperature**

For cool color appearance similar to natural daylight

- **Variety of Lamp Types**

4', 8' and U-Bent Rapid Start, Econ-o-watt®, Instant Start and High Output types

- **Excellent Color Rendering**

84 CRI

- **ALTO® Lamp Technology in 4-Foot Econ-o-watt Lamps**

TCLP compliant—

Reduction in mercury content of more than 80% when compared to standard fluorescent lamps

Green End Caps® allow for product differentiation at time of purchase and at end of lamp life

Green End Caps are a registered trademark of Philips Electronics North America Corporation.



Daylight Deluxe Fluorescent Lamps

Electrical, Technical and Ordering Data (Subject to change without notice)

Product Number	Description	Nominal Watts	Bulb	Base	Std. Pkg. Qty.	Color Temp. (Kelvin)	Color Rendering Index (CRI)	Nominal Length (Inches)	Rated Average Life ⁽¹⁾ (Hrs)	Approx. Initial Lumens	Design Lumens ⁽²⁾
+ 26659-3	F40DX/RS/EW/ALTO	34	T12	Med. Bipin	30	6500	84	48	20,000	2025	1775
22719-9	F40DX	40	T12	Med. Bipin	30	6500	84	48	20,000	2325	2025
22044-2	F40DX UPC	40	T12	Med. Bipin	30	6500	84	48	20,000	2325	2025
+ 28868-8	F40DX 15/2PK	40	T12	Med. Bipin	30	6500	84	48	20,000	2325	2025
21993-1	FB40DX/6	40	T12	Med. Bipin	12	6500	84	22 7/8	18,000	2250	1950
21488-2	F96T12/DX/EW	75	T12	Single Pin	15	6500	84	96	12,000	4200	3675
21487-4	F96T12/DX	75	T12	Single Pin	15	6500	84	96	12,000	4500	3950
+ 28866-2	F96T12/DX UPC	75	T12	Single Pin	15	6500	84	96	12,000	4500	3950
+ 29282-1	F96/DX 8/2PK	75	T12	Single Pin	16	6500	84	96	12,000	4500	3950
21471-8	F96T12/DX/HO/EW	95	T12	RDC	15	6500	84	96	12,000	5850	5000
21489-0	F96T12/DX/HO	110	T12	RDC	15	6500	84	96	12,000	6750	5800

(1) Average life under specified test conditions with lamps turned off and re-started once every three operating hours

(2) Approximate lumens at 40% of rated average life

☉ This Lamp features ALTO Lamp technology

+ New since last printing

Shipping Data

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs)	Case Cube (cu. ft.)	Pallet Qty.	SKU's Per Layer	Layers High	SKU Dimensions (WxDxH) (Inches)	Case Dimensions (WxDxH) (Inches)	Pallet Dimensions (WxDxH) (Inches)
22044-2	22044-0	22044-5	30	18.68	2.45	720	120	6	1.5 x 1.5 x 47.75	10.38 x 8.25 x 49.38	41.5 x 49.5 x 49.38
28868-8	28868-6	28868-1	30	18.68	2.34	300	60	5	3.188 x 1.688 x 48.56	9.375 x 8.75 x 49.375	37.48 x 43.75 x 49.38
28866-2	28866-2	28866-7	15	20	2.7	675	75	9	1.5 x 1.5 x 93.75	9 x 5.437 x 95.437	45 x 48.94 x 95.44
29282-1	29282-9	29282-4	16	24.32	2.63	288	24	12	3.125 x 1.563 x 94.313	12.937 x 3.687 x 95.437	38.812 x 44.28 x 95.44

Spectral Power Distribution

