

ALUline PRO III

Large-diameter low-voltage reflector lamps for even more flexibility in accent lighting



Ideal for accent lighting in retail displays, exhibition halls in art galleries, and museums



► Highly Attractive Design

Large-diameter (111mm) low-voltage halogen reflector lamps with high-purity faceted aluminum reflector

► Homogeneous Beam and Comfortable Glare Free Light

A metal cap shields the filament to reduce direct glare and also eliminates direct light, producing a smooth beam with a very sharp contrast

► UV Block

UV block quartz reduces fading of goods on display

► 3000 Hour Rated Average Life

► Multiple Connection Options

The lamp can be connected in three ways: to a dedicated G53 socket or by direct wire connection to screw or push-in terminations on the lamp

► Low Pressure—12V for Open Fixtures

Low-pressure halogen burner technology permits the lamp to be safely used in open luminaires

PHILIPS

Philips Lighting Company
 200 Franklin Square Drive
 P.O. Box 6800
 Somerset, NJ 08875-6800
 1-800-555-0050

www.philips.com

Philips Lighting
 281 Hillmount Road
 Markham, Ontario
 Canada L6C 2S3
 1-800-555-0050

A Division of Philips Electronics North America Corporation

A Division of Philips Electronics Ltd.

Printed in USA 10/04

P-5641

ALUline PRO III

Electrical, Technical and Ordering Data (Subject to change without notice)

| Product Number | Description | Watts | Volts | Bulb | Base | Color Temp. (Kelvin) | Lumens | Beam Spread | Rated Avg. Life (Hrs.) | Candlepower |
|----------------|-----------------------------|-------|-------|-------------|------|----------------------|--------|-------------|------------------------|-------------|
| 13396-6 | ALUline IMM 50W G53 12V 8D | 50 | 12 | ALU Pro III | G53 | 3000K | 950 | 8 | 3000 | 23,000 |
| 13397-4 | ALUline IMM 50W G53 12V 24D | 50 | 12 | ALU Pro III | G53 | 3000K | 950 | 24 | 3000 | 4000 |
| 13398-2 | ALUline IMM 75W G53 12V 8D | 75 | 12 | ALU Pro III | G53 | 3000K | 1575 | 8 | 3000 | 30,000 |
| 13399-0 | ALUline IMM 75W G53 12V 24D | 75 | 12 | ALU Pro III | G53 | 3000K | 1575 | 24 | 3000 | 5300 |
| 13400-7 | ALUline IMM 75W G53 12V 45D | 75 | 12 | ALU Pro III | G53 | 3000K | 1575 | 45 | 3000 | 1900 |

Shipping Data (Subject to change without notice)

| Product Number | SKU UPC (87-11500) | Outer Bar Code (5-00-46677) | Case Qty. | Case Weight (lbs.) | Case Cube (cu. ft.) | Pallet Qty. | SKUs Per Layer | Layers High | SKU Dimensions (W x D x H) (In.) | Case Dimensions (W x D x H) (In.) | Pallet Dimensions (W x D x H) (In.) |
|----------------|--------------------|-----------------------------|-----------|--------------------|---------------------|-------------|----------------|-------------|----------------------------------|-----------------------------------|-------------------------------------|
| 13396-6 | 42652-9 | 13396-7 | 6 | 1.41 | 0.23 | 1104 | 138 | 8 | 3.38 x 3.38 x 4.44 | 10.67 x 7.32 x 5.16 | 50 x 36.6 x 41.28 |
| 13397-4 | 42655-0 | 13397-4 | 6 | 1.41 | 0.23 | 1104 | 138 | 8 | 3.38 x 3.38 x 4.44 | 10.67 x 7.32 x 5.16 | 50 x 36.6 x 41.28 |
| 13398-2 | 42698-7 | 13398-1 | 6 | 1.41 | 0.23 | 1104 | 138 | 8 | 3.38 x 3.38 x 4.44 | 10.67 x 7.32 x 5.16 | 50 x 36.6 x 41.28 |
| 13399-0 | 42700-7 | 13399-8 | 6 | 1.41 | 0.23 | 1104 | 138 | 8 | 3.38 x 3.38 x 4.44 | 10.67 x 7.32 x 5.16 | 50 x 36.6 x 41.28 |
| 13400-7 | 42702-1 | 13400-1 | 6 | 1.41 | 0.23 | 1104 | 138 | 8 | 3.38 x 3.38 x 4.44 | 10.67 x 7.32 x 5.16 | 50 x 36.6 x 41.28 |

