

Philips Halogená® Vanity Globe

Adds bright, white light for a decorative touch



► Superior Light Quality

- Provides a bright, white light
- Dimmable: Maintains a high light quality when dimmed

► Variety of Finishes

- White: Designed to provide light with a reduced glare
- Clear: Designed to provide spectacular sparkle

► Lasts 3 Years¹

1) Lasts 3 years based on 2½ hours average usage per day/7 days per week.

Ideal for bathroom vanity strips, hanging pendants, and decorative lighting fixtures



PHILIPS

Philips Lighting Company
200 Franklin Square Drive
P.O. Box 6800
Somerset, NJ 08875-6800
1-800-555-0050

www.philips.com

Philips Lighting
281 Hillmount Road
Markham, Ontario
Canada L6C 2S3
1-800-555-0050
A Division of Philips Electronics Ltd.

A Division of Philips Electronics North America Corporation
Printed in USA 05/06 P-8582

Philips Halogená® Vanity Globe

Electrical, Technical and Ordering Data (Subject to change without notice)

Product Number	Product Description	Product Name	Bulb Finish	Nominal Watts	Bulb	Base Type	Volts	Operating Position	Published Lumens	M.O.L. (In.)	Rated Avg. Life, Hours ¹	Life, Years ²
I5023-5	40G25/W/HAL	Vanity	White	40	G25	Medium	120	Any	475	4 7/16	3000	3
I5025-0	60G25/W/HAL	Vanity	White	60	G25	Medium	120	Any	870	4 7/16	3000	3
I5024-3	40G25/CL/HAL	Vanity	Clear	40	G25	Medium	120	Any	500	4 7/16	3000	3
I5026-8	60G25/CL/HAL	Vanity	Clear	60	G25	Medium	120	Any	990	4 7/16	3000	3

Ordering and Shipping Data

Product Number	Product Description	UPC Code (0 46677-)	Case Bar Code (5 00 46677-)	Case Qty.	SKU Dimensions (W x D x H)(In.)	Case Dimensions (W x D x H)(In.)	Case Cube (cu. ft.)	Case Wt. (lbs.)	SKUs Per Layer	No. of Layers	Cases Per Pallet	Pallet Dimensions (W x D x H)(In.)
I5023-5	40G25/W/HAL	15023 5	15023 0	3/2	3.1 x 6.3 x 4.3	7.1 x 10 x 4.6	0.19	1.20	72	10	240	40 x 42.8 x 46.3
I5025-0	60G25/W/HAL	15025 9	15025 4	3/2	3.1 x 6.3 x 4.3	7.1 x 10 x 4.6	0.19	1.20	72	10	240	40 x 42.8 x 46.3
I5024-3	40G25/CL/HAL	15024 2	15024 7	3/2	3.1 x 6.3 x 4.3	7.1 x 10 x 4.6	0.19	1.20	72	10	240	40 x 42.8 x 46.3
I5026-8	60G25/CL/HAL	15026 6	15026 1	3/2	3.1 x 6.3 x 4.3	7.1 x 10 x 4.6	0.19	1.20	72	10	240	40 x 42.8 x 46.3

1) Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

2) Lasts 3 years based on 2½ hours average usage per day/7 days per week.

CAUTION: Before using bulb, see operating instructions on package. Adherence to the operating instructions will reduce the risk of personal injury or fire. The filament capsule contained inside this glass bulb is pressurized, operates at high temperature and could unexpectedly shatter. Should the outer bulb break, particles of extremely hot glass could be discharged into the fixture and/or around the surrounding environment, thereby creating a risk of personal injury or fire.

